

Order symbol: ARK12106CHSSLM
Product nbr: 8561542
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S. Lockable latch. Base includes 1/2 and 3/4 inch knock-outs and metal mounting feet.

EAN: 6418074097187
EI. number:
Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	305	254	152	ALBP1210	Aluminum Back Panel
inch:	12.0	10.0	6.0	ADFP1210	Dead Front Panel w/ screws
Materials:				ASP1210	Aluminum Swing Panel
Material:	Polycarbonate			ASPK1210	Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPHK12	Swing Panel Kit w/o Panel
Cover screws material:	Stainless steel			AMFL10	10" Mounting Flange Set
Cover colour:	RAL 7035 -light grey			Rating:	
Gasket material:	Polyurethane			Ingress Protection (EN 60529): IP66/IP67	
Temperatures:				Impact Resistance (EN 62262): IK09	
Temperature °C (short term):	-40 ... 140 °C			Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 284 °F			UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F			Flammability Rating: UL 508	
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
ABP1210	Painted Steel Back Panel			NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	

