



Cleanly strips 22 to 24 (.34 to .25 mm2) AWG wire. Convenient insulation crushing slot. Curved handles provide greater tool control. Comfortable plastic-dipped handles.

Specifications

Overall Length:	6" (152.4 mm)	Jaw Length:	1.25" (31.8 mm)
Jaw Width:	0.688" (17.5 mm)	Jaw Thickness:	3/8" (9.5 mm)
Point Diameter:	1/16" x 3/32" (1.6 mm x 2.4 mm)	Handle Colour:	Yellow
Handle Finish:	Plastic-dipped	Weight:	0.25 l b (0.11 kg)