

RAS-LP4

Specifications and dimensions



- 22mm lamp holder
- Transformer type

Features	
Width	30mm
Depth behind panel	40mm
Depth behind panel	56mm
Weight	0.1Kg
Input voltage	240V AC
Lamp (BA9) voltage	6V
Transformer rating	1.2VA
Related products	
Mounting collar (supplied)	RAS-FB
Lamp head	RAS-LP

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>