

## 7.0mm x 109mm Cobalt Ground Jobber Drill

Code	GCI070
Size (Dia)	7.0mm
Overall Length	109mm
Cutting Angle	135 Degree Split Point
Pack Qty	1
Packaging	Plastic Blister on Card
Weight	36g
Barcode	5039197035477



### Description

Professional quality, fully ground 5% (M35) Cobalt drill bits  
M35 (5% Cobalt) High Speed Steel increases Heat and Wear Resistance  
For drilling very hard, dense metals such as stainless steels, high tensile steels and cast iron.  
135° Split Point Tip for easy drill start without Skidding  
Manufactured to DIN338 standard

### Applications

For drilling high tensile steels, stainless steel, steel, cast iron and other "Tough to Drill" metals  
**Always use Cutting oil / spray when drilling metals**

### Suitable For

For use with all makes of pillar drills, mains powered and cordless rotary drills.