

M8-PCB-THT-2PC-4P-DCOD-F-ANG-SHLD



Part number	21 42 000 0019
Specification	M8-PCB-THT-2PC-4P-DCOD-F-ANG-SHLD
HARTING eCatalogue	https://b2b.harting.com/21420000019

Identification

Category	Connector
Series	Circular connectors M8
Element	PCB connector
Specification	Angled
Description of hood/ housing	13 mm

Version

Termination method	Wave soldering termination
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	D-coding

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Contact resistance	≤10 mΩ
Ambient temperature	-30 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 IP67
Transmission characteristics	Cat. 5 Class D up to 100 MHz

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated



Pushing Performance

Specifications and approvals

Specifications	IEC 61076-2-114
----------------	-----------------

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85366990