

Neo-Light

Dual Color LED Task Lamp

3-Year

60 Ultra-LEDs

Touch-

Lamp Head

Tilt



Innovative Illumination

Aven's Neo-Light LED Task Lamp offers ultra-bright, even illumination for your work bench. This modern, innovative design features 60 energy efficient LEDs with touch-sensitive buttons to control brightness and color temperature. Illuminate using warm light, white light, or both!

- Use the 30 warm LEDs, 30 white LEDs, or both!
- Brightness adjustment via touch-sensitive buttons
- Sleek, modern design
- Arm length approximately 25-inches

Perfect for a wide range of tasks



30 warm LEDs

30 white LEDs



NEO-LIGHT DUAL COLOR LED TASK LAMP

SKU	26536
BRIGHTNESS ADJUSTMENT	Via touch-sensitive buttons
LUMENS	Max 980lm
REACH	Approx. 25in
COLOR TEMPERATURE	3500K-6500K
ILLUMINATION	30 white and 30 warm LEDs
POWER SUPPLY	Input: 100-240V AC 50~60Hz Output: 20V
ACCESSORIES INCLUDED	10lb table base, power supply