



TRIAx

connecting the future



LTE WFAV 425 - 1 Input - Wideband Masthead Amplifier & Power Supply Kit

Article number: 370562

Product description:

Wolsey LTE Masthead Amplifier Kit

- F-Connector Masthead Amplifier and Power Supply Kit
- 1 Input 4 Output
- 10-25 dB Variable Gain
- Weatherproof housing
- Fully screened enclosure

Specifications

ORDER INFORMATION	
EAN Number	5702663705623
CHARACTERISTICS	
Type	Amplifier - mast
Max. Output level @ -60 dB IMD	85 dB μ V
FREQUENCY	
Input 1 - frequency	470...790 MHz
Input 1 - band	UHF (T)

Input 1 - channels	21...60
LTE protection	@ 800Mhz
GAIN	
Input 1 - gain	10-25 dB
Input 1 - noise figure	<2.2 dB
RETURN LOSS	
Return Loss	10 Typ dB
ELECTRICAL	
Impedance	75 Ω
OPERATIONAL	
DC Operating voltage	12 VDC
DC Current consumption	100 mA
CONNECTORS	
Number of inputs	1
Number of outputs	4
Connector Type	F-female
MECHANICAL	
Product Height	215 mm
Product Depth	60 mm
Product Width	120 mm
Colour	Black
Packaging Height	0,070 m
Packaging Width	0,220 m
Packaging Depth	0,120 m
Packaging Volume	0,002 m ³
Net Weight	0,550 kg
Tara Weight	0,065 kg
Total Weight	0,615 kg
Remarks	Kit includes WPS 100 Power Supply, 12VDC, 100mA Max Fully screened