


REV.	DATE	DESCRIPTION
NC	08/30/04	INITIAL RELEASE



NO.	DESCRIPTION	MATERIAL	FINISH	QTY	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN () ARE IN INCHES AND FOR DETAILERS REFERENCE ONLY. TOLERANCES PER UNLESS OTHERWISE SPECIFIED ARE:	APPROVALS	DATE	PART DESCRIPTION		
8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN () ARE IN INCHES AND FOR DETAILERS REFERENCE ONLY. TOLERANCES PER UNLESS OTHERWISE SPECIFIED ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm 120mm AND OVER ± 0.75mm DIMENSIONS FOR HOLE ARE: Ø20 - .315 - ± 0.007" .315 - 1.180 - ± 0.015" 1.180 - 4.724 - ± 0.020" DO NOT SCALE DRAWINGS					Amphenol Connex BNC JACK TO MCX JACK ADAPTER 2422206
7										
6										
5										
4										
3	CONTACT PIN	BER, COPPER	GOLD	1						
2	INSULATOR BODY	TEFLON BRASS	NATURAL GOLD	1						
1										
	DESCRIPTION	MATERIAL	FINISH	QTY						

NO.	DESCRIPTION	MATERIAL	FINISH	QTY
8				
7				
6				
5				
4				
3	CONTACT PIN	BER, COPPER	GOLD	1
2	INSULATOR BODY	TEFLON BRASS	NATURAL GOLD	1
1				

NO.	DESCRIPTION	MATERIAL	FINISH	QTY
8				
7				
6				
5				
4				
3	CONTACT PIN	BER, COPPER	GOLD	1
2	INSULATOR BODY	TEFLON BRASS	NATURAL GOLD	1
1				