muRata Capacitor Data Sheet GQM2195C2E2R8DB12# "#" indicates a package specification code.



< List of part numbers with package codes > GQM2195C2E2R8DB12D

Shape

L size 2.0 ±0.15mm W size 1.25 ±0.15mm T size 0.85 ±0.15mm External terminal width e 0.2 to 0.7mm 0.7mm min. Distance between external terminals g 0805 (2012M) Size code in inch(mm)

References
nelelences

Packaging	Specifications	Minimum quantity
D	φ180mm Paper taping	4000

Mass (typ.)	
1 piece	9.5mg
φ180mm Reel	152g

Specifications

Capacitance	2.8pF ±0.5pF
Rated voltage	250Vdc
Temperature characteristics (complied standard)	C0G(EIA)
Temperature coefficient	0±30ppm/°C
Temperature range of temperature characteristics	25 to 125°C
Operating temperature range	-55 to 125°C

🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.