

## DMX-CONTROLLED RGBW LED BAR WITH 3 LED & REMOTE CONTROL

### LEDBAR3-RC

Compact LED bar fitted with 4-in-1 RGBW LEDs.

- 3 x 8W 4-in-1 RGBW LED
- 8 / 4-1 / 4 / 3 / 2 DMX channels
- Stroboscope 0-20Hz
- Auto, master-slave, DMX, sound or remote-controlled operation
- 4 control buttons with LED display
- Remote control

**EAN  
CODE**

**5420047136411  
16-2096**

### SPECIFICATIONS TECHNIQUES

Power supply	AC100~240V 50/60Hz
Consumption	24W
DMX channels	8 / 4-1 / 4 / 3 / 2
Light source	3 LED RVBB 4-in-1 de 8W
Beam angle	25°
Fuse	0.5A
Dimensions	1.2kg
Weight	287 x 86 x 104mm



### LOGISTICS VALUES

Packaging height	12 cm
Packaging width	14.5 cm
Packaging depth	34.5 cm
Packaging volume	0.006 m <sup>3</sup>
Packaging gross weight	800 kg
Qty per master carton	12
EAN14 code	54200471364118
Customs code	94054091

