

Han-Eco 16B-HTE-for SL-M25



Part number	19 43 016 0446
Specification	Han-Eco 16B-HTE-for SL-M25
HARTING eCatalogue	https://b2b.harting.com/19430160446

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Hoods

Version

Locking type	Single locking lever
Size	16 B
Version	Top entry
Cable entry	1x M25

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 61984 EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3
----------------	--

Commercial data

Packaging size	1
Net weight	157 g



Pushing Performance

Commercial data

Country of origin	Germany
European customs tariff number	85389099