

Han-Eco 10B-HTE-for DL-M20-glanded



| | |
|--------------------|---|
| Part number | 19 43 110 0425 |
| Specification | Han-Eco 10B-HTE-for DL-M20-glanded |
| HARTING eCatalogue | https://b2b.harting.com/19431100425 |

Identification

| | |
|-----------------------------|-----------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-Eco® B |
| Type of hood/housing | Hoods |
| Description of hood/housing | With integrated cable gland |

Version

| | |
|--------------|----------------------|
| Locking type | Double locking lever |
| Size | 10 B |
| Version | Top entry |
| Cable entry | 1x M20 |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Number of relockings | ≥500 |
| Degree of protection acc. to IEC 60529 | IP66 |
| Clamping range | 6 ... 13 mm |

Material properties

| | |
|---|-------------------------------------|
| Material (hood/housing) | Polyamide Fibre-glass reinforced |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0 |

Specifications and approvals

| | |
|----------------|--|
| Specifications | IEC 61984 EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3 |
|----------------|--|



Pushing Performance

Commercial data

| | |
|--------------------------------|----------|
| Packaging size | 1 |
| Net weight | 119 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
