

Han-Eco 24B-HSM1-with DL-M32-glanded



| | |
|--------------------|---|
| Part number | 19 43 124 0232 |
| Specification | Han-Eco 24B-HSM1-with DL-M32-glanded |
| HARTING eCatalogue | https://b2b.harting.com/19431240232 |

Identification

| | |
|-----------------------------|-----------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-Eco® B |
| Type of hood/housing | Surface mounted housing |
| Description of hood/housing | With integrated cable gland |

Version

| | |
|--------------|----------------------|
| Locking type | Double locking lever |
| Size | 24 B |
| Version | Side entry |
| Cable entry | 1x M32 |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Number of relockings | ≥500 |
| Degree of protection acc. to IEC 60529 | IP66 |
| Clamping range | 13 ... 21 mm |

Material properties

| | |
|---|-------------------------------------|
| Material (hood/housing) | Polyamide Fibre-glass reinforced |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (seal) | NBR |
| Colour (seal) | RAL 9005 (jet black) |
| Material (locking) | Polyamide Fibre-glass reinforced |
| Colour (locking) | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0 |



Pushing Performance

Material properties

Material flammability class acc. to UL 94 (locking levers) V-0

Specifications and approvals

| | |
|----------------|-------------------------------|
| Specifications | IEC 61984 |
| | EN 45545-2 R22: HL1, HL2, HL3 |
| | EN 45545-2 R23: HL1, HL2, HL3 |
| | EN 45545-2 R24: HL1, HL2, HL3 |

Commercial data

| | |
|--------------------------------|----------|
| Packaging size | 1 |
| Country of origin | Germany |
| European customs tariff number | 85389099 |