

Han-Eco 24B-HSE-for SL-M40-glanded



Part number	19 43 124 0548
Specification	Han-Eco 24B-HSE-for SL-M40-glanded
HARTING eCatalogue	https://b2b.harting.com/19431240548

Identification

Category	Hoods/Housings
Series of hoods/housings Han-Eco [®] B	
Type of hood/housing	Hoods
Description of hood/ housing	With integrated cable gland

Version

Locking type	Single locking lever
Size	24 B
Version	Side entry
Cable entry	1x M40

Technical characteristics

Limiting temperature	-40 +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66
Clamping range	16 28 mm

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Product data sheet 19 43 124 0548 Han-Eco 24B-HSE-for SL-M40-glanded



Commercial data

Packaging size	1
Net weight	220 g
Country of origin	Germany
European customs tariff number	85389099