

## Han-Eco 10B Outd-HSM2-with DL-M32



Part number	19 43 210 0272
Specification	Han-Eco 10B Outd-HSM2-with DL-M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19432100272">https://b2b.harting.com/19432100272</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Surface mounted housing

### Version

Locking type	Double locking lever
Size	10 B
Version	Side entry
Cable entry	2x M32

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0

### Specifications and approvals

Specifications	IEC 61984 EN 45545-2 R22: HL1, HL2, HL3
----------------	--



Pushing Performance

## Specifications and approvals

	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3

## Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099