

## Han-Eco 16B Outd-HSM2-w. DL-M32-glanded



Part number	19 43 316 0272
Specification	Han-Eco 16B Outd-HSM2-w. DL-M32-glanded
HARTING eCatalogue	<a href="https://b2b.harting.com/19433160272">https://b2b.harting.com/19433160272</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Surface mounted housing
Description of hood/housing	With integrated cable gland

### Version

Locking type	Double locking lever
Size	16 B
Version	Side entry
Cable entry	2x M32

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66
Clamping range	13 ... 21 mm

### Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance

## Material properties

Material flammability class acc. to UL 94 (locking levers) V-0

## Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3

## Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099