



Pushing Performance

Han-Eco 24B Outd-HSM2-w. DL-M25-glanded



Part number	19 43 324 0271
Specification	Han-Eco 24B Outd-HSM2-w. DL-M25-glanded
HARTING eCatalogue	https://b2b.harting.com/19433240271

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Surface mounted housing
Description of hood/housing	With integrated cable gland

Version

Locking type	Double locking lever
Size	24 B
Version	Side entry
Cable entry	2x M25

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66
Clamping range	9 ... 17 mm

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance

Material properties

Material flammability class acc. to UL 94 (locking levers) V-0

Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099