

**KEMET Part Number: C0805Y104K5RACTU**  
(C0805Y104K5RAC7800)

SMD Comm X7R FF, Ceramic, Floating Electrode, 0.1 uF, 10%, 50 VDC, X7R, SMD, MLCC, FF-CAP, Floating Electrode, 0805



**Dimensions**

Dimension	Value
L	2mm +/-0.3mm
W	1.25mm +/-0.3mm
T	1.25mm +/-0.15mm
S	0.75mm MIN
B	0.5mm +/-0.25mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	2500

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	SMD Comm X7R FF
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, FF-CAP, Floating Electrode
<b>Features:</b>	FF-CAP, Floating Electrode
<b>RoHS:</b>	Yes
<b>Termination:</b>	Flexible Termination
<b>Marking:</b>	No
<b>Miscellaneous:</b>	Note: Referee time for X7R dielectric for this part number is 1000 hours
<b>Chip Size:</b>	0805

**Specifications**

<b>Capacitance:</b>	0.1 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	50 VDC
<b>Dielectric Withstanding Voltage:</b>	125 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	X7R
<b>Dissipation Factor:</b>	2.50% 1kHz 25C
<b>Aging Rate:</b>	3% Loss/Decade Hour
<b>Insulation Resistance:</b>	10 GOhms