## KEMET Part Number: SU9H-02080

(UALSU9H0208000)



**General Information** 

SU-9V/9H

Yes

Κ

250 VAC

8000 uH

200 mA

6 Ohms

-25/+125C

**Specifications** 

Through-Hole

Temperature Rise Maximum: 40

Series:

Style:

RoHS:

Miscellaneous:

Voltage AC:


Inductance:

Temperature Range:

DC Resistance:

Current:

## KEMET, SU-9V/9H, AC Line Filters, Common Mode, 8000 uH



Dimensions	
L	17mm MAX
Т	15.5mm MAX
Н	12.5mm MAX
LL	4mm MIN
S	7mm +/-0.5mm

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	1000
Weight:	3.2 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and	
we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the	
requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us	
with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.	

