

NEUTRIK



NE8MX-TOP

Cable connector carrier consists of a velour chromium shell, chuck and boot. The boot is suitable for cable diameters from 5 - 8 mm. For non pre-assembled cables only. Cable connector carrier does not include a RJ45 plug.

The etherCON cable connector carrier upgrades a conventional RJ45 connector to an extremely robust, outdoor protected lockable solution (IP65 & UL50E).

ATTENTION: Does not intermate with the CAT6 chassis connectors NE8FDY-C6 and NE8FDY-C6-B.

Features and Benefits

- The RJ45 system for harsh and demanding environment
 - Cable connector carrier accepts the most common RJ45 plugs (see list at [downloads](#))
-
- Rugged diecast shell and unique chuck type strain relief

- Protects Ethernet connections in a variety of commercial type applications and is designed to prevent breakage of the fragile components of standard RJ45 connectors
- Allows assembly of pre-assembled conventional RJ45 cables
- Accessories include color coded boots in 9 standard colors

Technical Information

Product	
Title	NE8MX-TOP
Gender	male
IMPORTANT	Cable connectors do not include RJ45 plug. RJ45 cable assembly must be provided by end user!
Mechanical	
Cable O.D.	5.0 - 8.0 mm
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Material	
Boot	UV-resistant rubber
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Velour Chromium
Strain relief	Polyacetal (POM)

Environmental

Temperature range	-30 °C to +80 °C
Protection class	IP65, UL50E (mated)