

## Accessories - PTCM-MP-PI 0,34-0,75 - 1013989


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 055626 492957
GTIN	4055626492957
Weight per Piece (excluding packing)	0.400 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### General

Range of articles	PTCM-MP-PI
-------------------	------------

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 5.1	27260700
eCl@ss 6.0	27260700

## Accessories - PTCM-MP-PI 0,34-0,75 - 1013989

### Classifications

#### eCl@ss

eCl@ss 7.0	27440309
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

#### ETIM

ETIM 5.0	EC000796
ETIM 6.0	EC002638

### Accessories

#### Accessories

#### Crimping tool

Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998



Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm<sup>2</sup>. Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

---

### Additional products

Printed-circuit board connector - PTCM 0,5/ 2-PI-2,5 WH - 1015242



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 2, pitch: 2.5 mm, connection method: Crimp connection, color: white

---

Printed-circuit board connector - PTCM 0,5/ 3-PI-2,5 WH - 1015243



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 3, pitch: 2.5 mm, connection method: Crimp connection, color: white

## Accessories - PTCM-MP-PI 0,34-0,75 - 1013989

### Accessories

Printed-circuit board connector - PTCM 0,5/ 4-PI-2,5 WH - 1015244



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, connection method: Crimp connection, color: white

---

Printed-circuit board connector - PTCM 0,5/ 5-PI-2,5 WH - 1015245



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 5, pitch: 2.5 mm, connection method: Crimp connection, color: white

---

Printed-circuit board connector - PTCM 0,5/ 6-PI-2,5 WH - 1015246



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 6, pitch: 2.5 mm, connection method: Crimp connection, color: white

---

Printed-circuit board connector - PTCM 0,5/ 7-PI-2,5 WH - 1015247



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 7, pitch: 2.5 mm, connection method: Crimp connection, color: white

---

Printed-circuit board connector - PTCM 0,5/ 8-PI-2,5 WH - 1015248



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 8, pitch: 2.5 mm, connection method: Crimp connection, color: white

---

---

