

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010844032](#)
Status: **Active**
Overview: [MLX Power Connectors](#)
Description: 6.35mm Pitch MLX Power Connector, 2.13mm Contact Diameter, Vertical, PA Polyamide (Nylon) 6/6, Tin (Sn), White, 3 Circuits

Documents:

| | |
|--|--|
| 3D Model | Packaging Specification PK-43255-001-001 (PDF) |
| Drawing (PDF) | Packaging Specification PK-43255-003-001 (PDF) |
| Product Specification PSX-42002-0001-001 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|--|
| Product Family | PCB Headers |
| Series | 42002 |
| Application | Power, Wire-to-Board |
| Comments | High Vibration Application, High Vibration Application |
| Overview | MLX Power Connectors |
| Product Name | MLX |
| UPC | 800753610736 |

Physical

| | |
|--------------------------------|-----------------|
| Breakaway | No |
| Circuits (Loaded) | 3 |
| Circuits (maximum) | 3 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 50 |
| Flammability | 94V-2 |
| Glow-Wire Capable | No |
| Lock to Mating Part | Yes |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 1.960/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| PC Tail Length | 4.30mm |
| PCB Retention | None |
| PCB Thickness - Recommended | 0.90mm |
| Packaging Type | Carton |
| Pitch - Mating Interface | 6.35mm |
| Polarized to PCB | Yes |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -55° to +105°C |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|--------------|
| Current - Maximum per Contact | 13.5A, 20.0A |
| Voltage - Maximum | 600V |

Solder Process Data

| | |
|--|------|
| Duration at Max. Process Temperature (seconds) | 010 |
| Lead-free Process Capability | WAVE |
| Process Temperature max. C | 260 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42002 Series](#)

Mates With

[42021](#) , [42023](#)

Material Info

Engineering Number

A-42002-3A2A1

Reference - Drawing Numbers

Packaging Specification

PK-43255-001-001, PK-43255-003-001

Product Specification

PSX-42002-0001-001

Sales Drawing

SDA-42002-XXXXX

This document was generated on 03/27/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION