

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191930078**  
**Status:** **Active**  
**Overview:** VersaKrimp Terminals and Splices  
**Description:** VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire

**Documents:**

[3D Model](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series 19193  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview VersaKrimp Terminals and Splices  
 Product Name VersaKrimp  
 Type Ring  
 UPC 800755049206

**Physical**


Barrel Type Closed - Brazed  
 Insulation None  
 Material - Plating Mating Tin  
 Net Weight 0.689/g  
 Packaging Type Bag  
 Stud Size 5-6 (M3-3.5)  
 Wire Size AWG 14, 16  
 Wire Size mm<sup>2</sup> 1.30-2.00

**Material Info**

Engineering Number BB-337-06

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing BBCD30101



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

19193 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

PremiumGrade Hand	<u>640030100</u>
Crimp Tool	
Crimp Head for the	<u>640070100</u>
AT-200 Pneumatic	
Hand Tool	