

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0193240007

Status:

Active

Overview:

Metric Ring Terminals

Description:

Avikrimp Metric Ring Terminal for Stud Size 5-6 (M3-3.5), Insulated Barrel

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification

UL

E32244

General

Product Family

Series

Crimp Quality Equipment

Mil-Spec

Overview

Product Name

Type

UPC

Ring and Spade Terminals

19324

Yes

N/A

Metric Ring Terminals

Avikrimp

Ring

887191290072

Physical

Barrel Type

Flammability

Insulation

Material - Metal

Material - Plating Mating

Net Weight

Packaging Type

Stud Size

Wire Size AWG

Closed - Brazed

94V-2

Nylon (PA)

Copper Alloy

Tin

0.892/g

Bag

M3.5

N/A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

BB2,5-823-M3,5

Reference - Drawing Numbers

Sales Drawing

SD-19324-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/88/2018 (15

January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19324 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description        | Product # |
|--------------------|-----------|
| PremiumGrade Hand  | 640010100 |
| Crimp Tool         |           |
| Crimp Head for the | 640050100 |
| AT-200 Pneumatic   |           |
| Hand Tool          |           |

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION