

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190990050**
Status: **Active**
Overview: Solderless Terminals
Description: InsulKrimp Snap Spade Terminal for 10-12 AWG Wire, Yellow

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-009-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series 19099
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview Solderless Terminals
 Product Name InsulKrimp
 Type Spade Snap
 UPC 800753089488

Physical

Barrel Type Closed
 Color - Resin Yellow
 Flammability 94V-0
 Insulation PVC
 Material - Plating Mating Tin
 Net Weight 1.645/g
 Packaging Type Bag
 Stud Size 10 (M5)
 Wire Insulation Diameter 6.40mm max.
 Wire Size AWG 10, 12
 Wire Size mm² 3.30-5.00

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number C-2719-10X

Reference - Drawing Numbers

Product Specification PS-19902-009-001, PS-19902-011-001,
 PS-19902-013-001
 Sales Drawing CCD20503



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19099 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade Hand Crimp Tool	<u>640010100</u>
Hand Crimp Tool	<u>640010300</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050300</u>