

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0310681011](#)
Status: **Active**
Overview: H-DAC 64 Unsealed Connector System
Description: 2.54mm H-DAC 64, 4 Way Receptacle Assembly, Single Row, Polarization B

Documents:

| | |
|--|--|
| 3D Model | Packaging Specification PK-30907-737 (PDF) |
| Drawing (PDF) | Packaging Specification PK-31301-076 (PDF) |
| Product Specification PS-31100-0001-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification AS-31067-100-001 (PDF) | |



General

| | |
|----------------|--|
| Product Family | Crimp Housings |
| Series | 31068 |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Comments | Polarization Option B, Gray, Polarization Option B, Gray |
| Overview | H-DAC 64 Unsealed Connector System |
| Product Name | H-DAC 64 |
| UPC | 756054315187 |

Physical

| | |
|-------------------------------|---------------------------------|
| Circuits (maximum) | 4 |
| Color - Resin | Gray, White |
| Gender | Receptacle |
| Glow-Wire Capable | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | Modified Polystyrene, Polyester |
| Net Weight | 1.385/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Polarized to Mating Part | Yes |
| Ports | 1 |
| Stackable | No |
| Temperature Range - Operating | -40° to +100°C |

Electrical

| | |
|-------------------------------|-------------|
| Current - Maximum per Contact | 11.0A, 9.0A |
|-------------------------------|-------------|

Solder Process Data

| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|----------------------------|
| Application Specification | AS-31067-100-001 |
| Packaging Specification | PK-30907-737, PK-31301-076 |
| Product Specification | PS-31100-0001-001 |
| Sales Drawing | SD-31109-003 |

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

31068 Series

Mates With

HDAC 64, 4 Way Male Housing Assembly
[310681041](#) , [310681071](#) , [311000041](#) ,
[311010041](#)

Use With

See Product Specification