

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009501071](#)
Status: **Active**
Overview: [SPOX Connector System](#)
Description: 3.96mm Pitch SPOX Crimp Housing, Female, with Friction Ramp, 7 Circuits, Natural

Documents:

3D Model	Product Specification PS-5195-006-001 (PDF)
Drawing (PDF)	Product Specification PS-5195-007-001 (PDF)
Product Specification PS-5195-003 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-5195-005-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	5195
Application	Signal, Wire-to-Board
Overview	SPOX Connector System
Product Name	SPOX
UPC	800753640719

Physical

Circuits (maximum)	7
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	1988.600/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Engineering Number	5195-07
--------------------	---------

Reference - Drawing Numbers

Product Specification	PS-5195-003, PS-5195-005-001, PS-5195-006-001, PS-5195-007-001
Sales Drawing	SD-5195-N



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5195 Series](#)

Mates With

[5272](#) , [5273](#) , [5274](#) right angle PCB header,
[5096](#) , [53405](#) , [5271](#)

Use With

[5194](#) , [5225](#)