

USB-C Multiport Adapter with Wireless Presenter Remote

Product ID: BNDDKTCHVPRS



This convenient bundle combines StarTech.com's [DKT30CHV](#) and [PRESREMOTE](#) equipped with a laser pointer. You can create a permanent or temporary workstation virtually anywhere you go and deliver professional presentations in any meeting or conference room.

Create a Mobile Workstation

This versatile USB-C multiport adapter for laptops makes it easy to create a mobile workstation when you need it most. It features HDMI and VGA ports, so you can easily connect a 4K HDMI or a standard-definition VGA monitor.

Installation is fast and easy, with native support in most operating systems. Plus, the adapter integrates a Gigabit Ethernet port and an additional USB 3.0 port, so you can access a wired network, or connect an additional USB peripheral to your laptop.

The host laptop USB-C port must support DP Alt Mode.

Deliver Professional Presentations

The presentation remote features a sleek, ergonomic design with a wireless range of 90 feet (27 m) and includes the required batteries and a carrying case. The USB receiver is supported by generic HID drivers, ensuring it will work with virtually any Mac or Windows computer.

With a built-in laser pointer, the presentation remote lets you guide your audience's attention to critical information in your on-screen content. It's perfect for PowerPoint presentations, websites or any other visuals you want to share with an audience.

The BNDDKTCHVPRS bundle is backed by a two-year StarTech.com warranty and free lifetime technical support. Our knowledgeable Technical Advisory Team is multilingual and located at our head office.

Certifications, Reports and Compatibility



Applications

- Business Travelers
- Educational Institutions & Educators

Features

- Docking station bundle includes compact USB-C multiport adapter and wireless professional presentation remote
- USB-C multiport adapter supports a VGA or 4K HDMI display plus Ethernet and 1x USB 3.0 port
- The included wireless presentation remote has a range of up to 90' or 27 m
- Gives business travelers the essential connectivity tools they need to make effective boardroom or conference room presentations on the road

Hardware	Warranty	3 Years
	4K Support	Yes
	Bus Type	USB-C
	Chipset ID	Cypress - CYPD2122 Cypress - CYUSB3314 STMicroelectronics - STDP2650 Chrontel - CH7517 ASIX - AX88179
	Displays Supported	1
	Fast-Charge Port(s)	No
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
	Performance	
Auto MDIX	Yes	
Compatible Networks	10/100/1000 Mbps	
Full Duplex Support	Yes	
Maximum Analog Resolutions	2048 x 1280p - 30Hz (VGA)	
Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)	
Maximum Digital Resolutions	3840 x 2160p - 30Hz (HDMI) Lower resolutions are also supported.	
Remote Color	Black	
Remote Humidity	30%~80% RH	
Remote Interface	USB	
Remote Max Distance	27 m (90 ft.)	
Remote Operating Temperature	5°C to 45°C (41°F to 113°F)	
Remote Optical Power	1mW	
Remote Power	Battery Powered	
Remote Storage Temperature	5°C to 45°C (41°F to 113°F)	
Remote Warranty	2 Years	
Remote Wavelength	650+20 mm	
Remote Wireless Band	2.4 GHz	
Type and Rate	USB 3.0 - 5 Gbit/s	
UASP Support	Yes	
Connector(s)	Connector Type(s)	1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Male

		<p>1 - HDMI (19 pin) Female</p> <p>1 - VGA (15 pin, High Density D-Sub) Female</p> <p>1 - RJ-45 Female</p> <p>1 - USB Type-A (9 pin) USB 3.0 Female</p>
Software	OS Compatibility	<p>Windows® 7, 8, 8.1, 10</p> <p>macOS 10.10 to 10.14</p> <p>Chrome OS™</p>
Special Notes / Requirements	Note	<p>For MacBook host systems using macOS 10.12, version 10.12.6 or later is required to support this product.</p> <p>Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your laptop USB-C port supports DP alt mode.</p> <p>Only one video output port can be used at the same time (HDMI or VGA). If two displays are connected, the HDMI port takes priority.</p> <p>A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).</p> <p>USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.</p> <p>The remote is a class 2 laser product</p> <p>The USB-C port on your host must support DP Alt mode</p>
	System and Cable Requirements	<p>Host laptop with an available USB-C port (to ensure full functionality, the laptop's USB-C port must support DP alt mode).</p>
Power	Power Source	USB-Powered
Environmental	Humidity	5~95% RH (Non-condensing)
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-40°C to 70°C (-40°F to 158°F)
Physical Characteristics	Product Height	17.000
	Product Length	114.000
	Product Weight	192.000
	Product Width	54.000
Packaging Information	Shipping (Package) Weight	0.3 kg [0.7 lb]

Product appearance and specifications are subject to change without notice.