

Han 6EMC/B HTE M32 PFT SL



Part number	19 62 806 1122
Specification	Han 6EMC/B HTE M32 PFT SL
HARTING eCatalogue	https://b2b.harting.com/19628061122

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] EMC/B
Type of hood/housing	Panel feed through housing
Type	High construction

Version

Locking type	Single locking lever
Han-Easy Lock [®]	Yes
Size	6 B
Version	Top entry
Cable entry	1x M32
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0



Pushing Performance

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	263.7 g
Country of origin	China
European customs tariff number	8538900000