# XKBA1233CA

## XKBA light hoisting applications joystick controller



#### Main

Range of product	Harmony XK
Product or component type	Complete joystick controller
Product specific application	Light hoisting applications

## Complementary

oompromornary		
Device short name	XKB	
Bezel material	Metal	
Fixing collar material	Metal	
Sale per indivisible quantity	1	
Protective treatment	TC	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-2070 °C	
Overvoltage category	Class I IEC 61140	
Standards	EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14	
Operator position information	All positions	
Operator profile	Handle with zero position mechanical interlock	
Notch per direction	13 0-12°-20°-28° for each direction	
Mechanical durability	1000000 cycles	
Vibration resistance	6 gn 170 Hz IEC 60068-2-6	
Shock resistance	20 gn 11 ms IEC 60068-2-27	
Connections - terminals	Captive screw clamp terminals <= 2 x 1.5 mm <sup>2</sup> with cable end Captive screw clamp terminals <= 1 x 2.5 mm <sup>2</sup> without cable end Captive screw clamp terminals >= 1 x 0.5 mm <sup>2</sup>	
Short-circuit protection	10 A cartridge fuse gG EN/IEC 60947-5-1	
[lth] conventional free air thermal current	10 A EN/IEC 60947-5-1 10 A CSA C22.2 No 14 10 A UL 508	
[Ui] rated insulation voltage	500 V 3 IEC 60947-1	
Compatibility code	XKB	

### **Environment**