

Main

Bezel material	Chromium plated metal
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor
Range of product	K

Complementary

[In] rated current	10 A
Accessory / separate part destination	Non illuminated push-button
Cap/operator or lens colour	Black
Contact operation	Standard fingersafe
Contacts type and composition	2 NO + 2 NC
Electrical connection	Screw clamp terminal
Mounting support	Panel
Operator position information	3 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Size	30 mm
Type of operator	Maintained
Utilisation category	AC-15 DC-13

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
product certifications	CE UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03

Offer Sustainability

Sustainable offer status	785901821342
RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold