

ZA2BP3

pushbutton head - diameter Ø 22 - green - booted



Main

Range of product	Harmony XAC
Product or component type	Head for push-button
Component name	XACA

Complementary

Marking	Unmarked
Operator additional information	Booted
Cap/operator or lens colour	Green
Product compatibility	XACA..
Mounting location	Front of enclosure
Sale per indivisible quantity	1
Standards	EN/IEC 60204-32 EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn 10...500 Hz IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Overvoltage category	Class II IEC 61140
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK08 EN 50102
Product weight	0.025 kg

Environment