



### Main

Range of product	Harmony
Product or component type	Head for pilot light
Product specific application	For incandescent bulb
Cap/operator or lens colour	Yellow

### Complementary

Mechanical durability	1000000 cycles
Product weight	0.015 kg

### Environment

standards	EN/IEC 60947-5-1 CSA C22.2 No 14
protective treatment	TH
ambient air temperature for operation	-25...55 °C
ambient air temperature for storage	-40...70 °C
vibration resistance	15 gn (10...500 Hz) conforming to IEC 60068-2-6
shock resistance	100 gn conforming to IEC 60068-2-27
electrical shock protection class	Class II conforming to IEC 61140
overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

### Contractual warranty

Warranty period	18 months
-----------------	-----------