

DL1EDBS

steady incandescent bulb - BA 15d - 24 V AC/DC -
<= 5 W



Main

| | |
|---------------------------------------|---------------------------|
| Range compatibility | Harmony XVM Optimum |
| Accessory / separate part category | Lighting accessory |
| Accessory / separate part type | Incandescent bulb |
| Accessory / separate part designation | Incandescent bulb |
| Accessory / separate part destination | Beacon and indicator bank |
| Bulb base | BA 15d |
| Signalling type | Steady |
| [Us] rated supply voltage | 24 V AC/DC |
| Luminance | 650 cd/m ² |
| Sale per indivisible quantity | 10 |

Complementary

| | |
|------------------------|----------|
| Power dissipation in W | <= 5 W |
| Product weight | 0.007 kg |

Environment

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.