

DL1EDMS

steady incandescent bulb - BA 15d - 230 V AC/DC -
<= 5 W



Main

Range compatibility	Harmony XVM Optimum
Accessory / separate part category	Lighting accessory
Accessory / separate part type	Incandescent bulb
Accessory / separate part designation	Incandescent bulb
Accessory / separate part destination	Beacon and indicator bank
Bulb base	BA 15d
Signalling type	Steady
[Us] rated supply voltage	230 V AC/DC
Luminance	650 cd/m ²
Sale per indivisible quantity	10

Complementary

Power dissipation in W	<= 5 W
Product weight	0.007 kg

Environment

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.