



## Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCRB XCRA
Movement of operating head	Rotary
Type of operator	Square rod metal square rod 6 mm, L = 300 mm
Switch actuation	By any moving part
Type of approach	Lateral approach
Positive opening	With

## Complementary

Associated complete product	XCRA11 XCRA15 XCRB51 XCRA55 XCRB12 XCRA12 XCRB55 XCRA51 XCRB11 XCRB52 XCRB15 XCRA52
Product weight	0.029 kg

## Environment

Ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0903 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------