



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product compatibility	XCKD XCKP XCKT XCMD
Associated body	ZCD21 ZCD21M12 ZCD25 ZCD26 ZCD27 ZCD28 ZCD29 ZCD29M12 ZCD31 ZCD35 ZCD37 ZCD39 ZCMD21C12 ZCMD21L08R12 ZCMD21L08U78 ZCMD21L1 ZCMD21L2 ZCMD21L5 ZCMD21M12 ZCMD25L1 ZCMD25L2 ZCMD25L5 ZCMD29C12 ZCMD29L1 ZCMD29L2 ZCMD29L5 ZCMD37L1 ZCMD37L2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCMD37L5
 ZCMD39L1
 ZCMD39L2
 ZCMD39L5
 ZCMD41L1
 ZCMD41L2
 ZCMD41L5
 ZCMD61C12
 ZCMD61M12
 ZCMD69C12
 ZCMD81L1
 ZCMD81L2
 ZCMD81L5
 ZCP21
 ZCP21M12
 ZCP25
 ZCP26
 ZCP27
 ZCP28
 ZCP29
 ZCP29M12
 ZCP31
 ZCP35
 ZCP37
 ZCP39
 ZCT21G11
 ZCT21N12
 ZCT21P16
 ZCT25G11
 ZCT25N12
 ZCT25P16
 ZCT26G11
 ZCT26N12
 ZCT26P16
 ZCT27G11
 ZCT27N12
 ZCT27P16
 ZCT28G11
 ZCT28N12
 ZCT28P16

Movement of operating head	Multi-directional
Type of operator	Side cat"s whisker spring return metal (with nitrile boot)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------