



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ1 ZCKJ11 ZCKJ11H29 ZCKJ11H7 ZCKJ1H29 ZCKJ1H7 ZCKJ2 ZCKJ21 ZCKJ21H29 ZCKJ21H7 ZCKJ2H29 ZCKJ2H7 ZCKJ4 ZCKJ41 ZCKJ41H29 ZCKJ41H7 ZCKJ4H29 ZCKJ4H7 ZCKJ5 ZCKJ5H29 ZCKJ5H7 ZCKJ6 ZCKJ6H29 ZCKJ6H7 ZCKJ7 ZCKJ7H29 ZCKJ7H7 ZCKJ8 ZCKJ8H29 ZCKJ8H7 ZCKJ9

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ9H29
 ZCKJ9H7
 ZCKJD31
 ZCKJD31H29
 ZCKJD31H7
 ZCKJD35
 ZCKJD35H29
 ZCKJD35H7
 ZCKJD37
 ZCKJD37H29
 ZCKJD37H7
 ZCKJD39
 ZCKJD39H29
 ZCKJD39H7

Movement of operating head	Linear
Type of operator	Roller lever plunger spring return metal
Type of approach	Lateral approach 1 direction

Complementary

Switch actuation	By 30° cam
Positive opening	With
Product weight	0.195 kg
Head material	Metal

Environment

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Low temperature

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------