



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ6H29 ZCKJ6H7 ZCKJD37 ZCKJ21 ZCKJ4H7 ZCKJ41H29 ZCKJ8H29 ZCKJ9H7 ZCKJ1H29 ZCKJ41 ZCKJ2H7 ZCKJD39 ZCKJD31H29 ZCKJD31H7 ZCKJ7 ZCKJD39H7 ZCKJ11H7 ZCKJ8H7 ZCKJ7H7 ZCKJ1H7 ZCKJD37H7 ZCKJD35H7 ZCKJ5 ZCKJ21H7 ZCKJ4H29 ZCKJ5H7 ZCKJ2H29 ZCKJD35 ZCKJ11 ZCKJ2 ZCKJ6

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ5H29  
 ZCKJD37H29  
 ZCKJD39H29  
 ZCKJ11H29  
 ZCKJ21H29  
 ZCKJ9H29  
 ZCKJ41H7  
 ZCKJ4  
 ZCKJ1  
 ZCKJ8  
 ZCKJ7H29  
 ZCKJD35H29  
 ZCKJ9  
 ZCKJD31

Movement of operating head	Linear
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach 2 directions

### Complementary

Switch actuation	By 30° cam
Positive opening	With
Product weight	0.155 kg
Head material	Metal

### Environment

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Low temperature

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1136 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------