



1.S.0

High precision tweezers - SS - tips: straight, fine, superior finish. OAL: 120mm




4 3/4" 120 mm
Strong, straight, fine

Documents

 Body material TDS

Product included in the following kit/kits

Article code	Family	Category	Full description
K5HP1.S 	Tweezers	High precision tweezers	Kit of 5 High precision tweezers - SS: 1, 2A, 3C, 5, 7.

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes

Category	High precision tweezers
Kit	no
Tip style	1
Tip type characteristic	fine
Bent / angled / curved tip (y/n)	no
Reverse action	no
Handle serration(y/n)	no
Tip serration (y/n)	no
Locking system	no
ESD safe	no
Body material	S
Product OAL (mm - in)	120.00 - 4.724
Product width (mm - in)	10.00 - 0.394
Product height (mm - in)	11.00 - 0.433
Tip thickness A (mm - in)	0.10 - 0.004
Tip width B (mm - in)	0.15 - 0.006
Tip opening gap (mm - in)	8.00 - 0.315
Net weight (g-lb)	13 - 0.029
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com