



3C.S.0

High precision tweezers - SS - tips: straight, sharp, fine, superior finish. OAL: 110mm




4 1/4" 110 mm

As 3, short

Documents

 Body material TDS

Product included in the following kit/kits

| Article code | Family | Category | Full description |
|--|----------|-------------------------|---|
| K5HP1.S  | Tweezers | High precision tweezers | Kit of 5 High precision tweezers - SS: 1, 2A, 3C, 5, 7. |

Product Details

| | |
|------------------------------------|-----|
| Market - MEDICAL DEVICE | yes |
| Market - LIFE SCIENCE & MICROSCOPY | yes |
| Market - ELECTRONICS | yes |
| Market - WATCHMAKING & JEWELRY | yes |

| | |
|---|-------------------------|
| Category | High precision tweezers |
| Kit | no |
| Tip style | 3C |
| Tip type characteristic | fine, sharp |
| Bent / angled / curved tip (y/n) | no |
| Reverse action | no |
| Handle serration(y/n) | no |
| Tip serration (y/n) | no |
| Locking system | no |
| ESD safe | no |
| Body material | S |
| Product OAL (mm - in) | 110.00 - 4.331 |
| Product width (mm - in) | 9.50 - 0.374 |
| Product height (mm - in) | 11.00 - 0.433 |
| Tip thickness A (mm - in) | 0.10 - 0.004 |
| Tip width B (mm - in) | 0.20 - 0.008 |
| Tip opening gap (mm - in) | 8.00 - 0.315 |
| Net weight (g-lb) | 11 - 0.024 |
| RoHS compliant | yes |
| | |



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com