




4SG.CX.0

Biology tweezers - Superalloy Anti-Acid/Anti-Mag - serrated handles - tips: straight. extra fine. superior finish. OAL: 110mm



4 1/4" 110 mm
Extra fine tips

Documents

Body material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Category	High precision tweezers
Kit	no

Tip style	4
Bent / angled / curved tip (y/n)	no
Reverse action	no
Handle serration	line serrated
Tip serration (y/n)	no
Locking system	no
ESD safe	no
Body material	CX
Product OAL (mm - in)	110.00 - 4.331
Product width (mm - in)	10.00 - 0.394
Product height (mm - in)	11.00 - 0.433
Tip thickness A (mm - in)	0.03 - 0.001
Tip width B (mm - in)	0.06 - 0.002
Tip opening gap (mm - in)	7.00 - 0.276
Net weight (g-lb)	12 - 0.026
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland
T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com