

Accessories

Rittal RiCase – interior installation

Mounting angles for 482.6 mm (19")



For additional installation of sub racks.

Material:

Extruded aluminium section, clear chromated

Supply includes:

2 mounting angles
Assembly parts

Note:

1 pack of threaded inserts and 2 packs of mounting rails and spacers are required for depth-adjustable installation.

For enclosure height	Packs of	Model No. RC
1 U	2	3751.650
2 U	2	3751.660
3 U	2	3751.670
4 U	2	3751.680
6 U	2	3751.690
7 U	2	3751.640
9 U	2	3751.780
12 U	2	3751.790

Slide rails



To support heavy slide-in equipment.

Material:

1.5 mm sheet steel, yellow passivated

Supply includes:

2 slide rails, assembly parts

Note:

Threaded inserts should be ordered separately.

Enclosure depth	Packs of	Model No. RC
300 mm	2	3751.500
420 mm	2	3751.510
540 mm	2	3751.520

Threaded inserts



For fastening mounting angles, slide rails, mounting kits, cable trunking etc. Slides into the grooves of the side panels.

Material:

Extruded aluminium section, clear chromated

Supply includes:

8 threaded inserts

For enclosure height	Packs of	Model No. RC
1 U	8	3751.700
2 U	8	3751.710
3 U	8	3751.720
4 U	8	3751.730
6 U	8	3751.740
7 U	8	3751.750
9 U	8	3751.760
12 U	8	3751.770

Earthing set



For compliance with electrical protection measures; fits all Rittal RiCase enclosures.

Supply includes:

Insert strip, pointed grub screws, green/yellow connection lead, serrated washer, nut

Packs of	Model No. VC
4	3798.000

Mounting rails



- For depth-variable installation of the mounting angles.
- For static or pull-out installation of component shelves.

Material:

Aluminium, clear chromated

Supply includes:

2 mounting rails
Assembly part

For enclosure depth	Packs of	Model No. RC
420 mm	2	3751.410
540 mm	2	3751.420

Note:

Threaded inserts and spacers should be ordered separately.