



Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	647 mm
Nominal width	436 mm
Nominal depth	250 mm
Enclosure mounting	Wall mounted
Device composition	Lock 2 Door 1 Body 1 Mounting plate 1
Body type	Built-in canopy One piece moulded with notches in the rear
Door type	Plain
Lock type	3 mm double-bar lock

Complementary

Number of locks	2
Mounting plate description	Plain bakelite
Accessibility for operation	Front
Removable parts	Door by hinges Mounting plate by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey RAL 7035
Standards	NEMA classification 13 NEMA classification 4X IEC 62208

Product certifications	UL
------------------------	----

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Fire resistance	960 °C IEC 62208
Ambient air temperature for storage	-35...90 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1511 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations