



Main

| | |
|-----------------------------|---|
| Range | Spacial |
| Product name | Spacial S3D |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure nominal height | 1200 mm |
| Enclosure nominal width | 600 mm |
| Enclosure nominal depth | 300 mm |
| Door type | Plain |
| Mounting plate description | Plain |
| Type of gland plate | Standard |
| Installation accessory type | Wall-mounting |
| Device composition | Body 1 Mounting plate 1 Door with lock 1 Cable gland plate 1 |

Complementary

| | |
|-----------------------------|---|
| Body type | Single piece body Gutter-shaped front rail double sheet thickness |
| Number of doors | 1 front face |
| Door opening side | Reversible 120 ° |
| Lock type | 3 points lock, 3 mm double-bar |
| Accessibility for operation | Front |
| Removable parts | Door by hinges Cable gland plate by screws Mounting plate by fixing element |
| Material | Galvanised steel for mounting plate Steel for enclosure |
| Surface finish | Epoxy-polyester powder enclosure |

| | |
|------------------------|------------------------------------|
| Colour | Grey RAL 7035 enclosure : |
| Standards | IEC 62208 |
| Product certifications | DNV CUL UL LR GL BV |
| Product weight | 47.2 kg |

Environment

| | |
|-------------------------|------------------------------|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0810 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|