

## Han 3A-HAE-M25



Part number	19 20 003 1645
Specification	Han 3A-HAE-M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19200031645">https://b2b.harting.com/19200031645</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A <sup>®</sup>
Type of hood/housing	Hoods

### Version

Locking type	Single locking lever
Size	3 A
Version	Side entry
Cable entry	1x M25
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

## Specifications and approvals

Approvals DNV GL

## Commercial data

Packaging size 1

Net weight 80.5 g

Country of origin China

European customs tariff number 8538900000

eCl@ss 27440202 Shell for industrial connectors