

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



PCB connector, nominal current: 41 A, number of positions: 5, pitch: 7.62 mm, connection method: Push-in spring connection, color: green, contact surface: Tin

Figure shows a 4-pos. version with locking flange at position 3

Your advantages

- Tool-free lever principle enables time-saving connection and release of conductors with/without ferrules
- ☑ Clear lever positions provide reliable feedback on opened or closed clamping spaces
- Time-saving push-in connection when lever is closed
- ☑ Intuitive locking mechanism prevents accidental disconnection



Key Commercial Data

Packing unit	1 pc	
Minimum order quantity	25 pc	
GTIN	4 055626 522456	
GTIN	4055626522456	
Weight per Piece (excluding packing)	40.000 g	
Custom tariff number	85366990	
Country of origin	Poland	

Technical data

Product type	PCB plug
Approval	cULus Recognized
Rated voltage (IEC)	1000



Technical data

Rated current (IEC)	41	
Number of positions	5	
Pitch	7.62 mm	
Connection cross section	6	
Type of locking	Self-locking flange	
Connection method	Push-in spring connection	
Plug-in system	POWER COMBICON 6	
Product family	LPC 6/STL3	
Contact type	Female connector	
Color	green (6021)	
Contact surface material	Tin	
Number of connections	5	

Classifications

eCl@ss

eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 5.0	EC002638
ETIM 6.0	EC002638
ETIM 7.0	EC002638

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details



Approvals

Γ

cULus Recognized	http://database.ul.com/cgi-bin/XYV/template/L	ISEXT/1FRAME/index.htm E60425-20010727
	В	С
Nominal voltage UN	600 V	600 V
Nominal current IN	35 A	35 A
mm²/AWG/kcmil	18-8	18-8

Accessories

Accessories

Cable end sleeve

Ferrule - AI 6 -18 YE - 3200603

Ferrule, sleeve length: 18 mm, length: 26 mm, color: yellow

Coding element

Coding profile - CP-PC RD - 1701967



Coding profile, for plugging into the coding ribs of the plug at a later date, insulating material, color: Red

Crimping tool

Crimping pliers - CRIMPFOX CENTRUS 6S - 1213144



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Stripping tool



Accessories

Stripping tool - WIREFOX 10 - 1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

Additional products

Printed-circuit board connector - PC 6/ 5-GL3-7,62 - 1717036



PCB headers, nominal current: 41 A, number of positions: 5, pitch: 7.62 mm, color: black, contact surface: Tin, mounting: Wave soldering

Phoenix Contact 2019 © - all rights reserved http://www.phoenixcontact.com