

**Accessories**  
**ETA 1180 01 0.2A**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

Similar to illustration

**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

Type	ETA 1180 01 0.2A
Order No.	<a href="#">1278850000</a>
Version	Accessories, Circuit breaker, 0.2 A
GTIN (EAN)	4050118091458
Qty.	5 pc(s).

## Accessories ETA 1180 01 0.2A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	8.2 mm	Width (inches)	0.323 inch
Height	24.4 mm	Height (inches)	0.961 inch
Depth	52.3 mm	Depth (inches)	2.059 inch
Net weight	10.6 g		

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Material data

Colour black

### System specifications

Version Fuse cartridge

### Additional technical data

Installation advice Direct mounting Type of mounting Plugged

### Rating data

Rated voltage 64 V DC Rated current 0.2 A

### Classifications

ETIM 5.0	EC000886	ETIM 6.0	EC000035
eClass 6.2	27-14-20-90	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-20-01
eClass 9.1	27-14-20-01		

### Approvals

ROHS Conform

### Downloads

Engineering Data [EPLAN, WSCAD](#)  
 Engineering Data [STEP](#)  
 User Documentation [StorageConditionsTerminalBlocks](#)