

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0797581060**
Status: **Active**
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin Plated, 304.00mm, 28 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	<u>79758</u>
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade Crimp Terminals
Datasheet Order No	987651-2631
Overview	<u>Off-the-Shelf Pre-Crimped Leads</u>
Product Name	PicoBlade
UPC	191128292634

Physical

Cable Length	0.30m
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	5.000/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.04mm max.
Wire Size AWG	28
Wire/Cable Type	UL 1061

Material Info

Engineering Number	KAB2518L0.304V01
--------------------	------------------

Reference - Drawing Numbers

Sales Drawing	797581060-000
---------------	---------------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[79758 Series](#)

Use With

[51021 PicoBlade Crimp Housing](#)