



CPUAC1U1300 Universal Power Adapter

Your replacement or spare AC adapter for portable electronic equipment.

The CPUAC1U1300 Universal Power Adapter with USB 2.1 Quick Charge Technology can be used as a replacement or spare DC power adapter for electronics such as portable DVD players and other A/V products, tablets, and many other electronics devices.

The CPUAC1U1300 with 1300mA supports voltages of 3V, 4.5V, 5V, 6V, 7.5V, 9V, and 12V with both positive and negative polarity settings. Seven (7) adapter tips assure compatibility with most popular electronics. The CPUAC1U1300's convenient folding AC plug makes it easy to carry in a brief case, back pack, or luggage. The 5 ft. cord provides flexibility to where you operate your electronic equipment.

It is equipped with one (1) 2.1A USB port for charging tablets (including the iPad), smart phones, MP3 players, and digital cameras.

A One-Year Warranty ensures that this product has passed our highest quality standards in design, assembly, material and workmanship.

Typical Applications

- Cameras
- MP3 Players
- Smartphones
- Portable AV Products

Features

- 1300mA Universal Power Adapter
- Selectable Voltages: 3V, 4.5V, 5V, 6V, 7.5V, 9V, and 12V DC
- 7 Adapter Tips w/5 ft. Cord
- Quick Charge Technology
- (1) USB 2.1 Amp Charging Port
- Folding AC Plug
- 1-Year Warranty

CPUAC1U1300 Universal Power Adapter

Your replacement or spare AC adapter for portable electronic equipment.

GENERAL	
Product Type	Universal Power Adapter
INPUT	
Voltage	100Vac - 120Vac
Plug Type	NEMA 5-15R
Plug Style	Folding
OUTPUT	
Output Power	1300mA
Output Voltage (Selectable)	3V, 4.5V, 5V, 6V, 7.5V, 9V, 12Vdc
USB Charge Port - Total	1
USB Charging Amperage	2.1A
Adapter Tips (Qty.)	7
Output Cord Length (ft.)	5
INDICATORS	
LED	Power On
PHYSICAL	
Color	Black
Form Factor	Slimline
Enclosure Construction	ABS
Dimensions (WxHxD) (in.)	2.3 x 3.7 x 1.3
Weight (lbs.)	0.26
ENVIRONMENTAL	
Operating Temperature	32°F to 95°F / 0°C to 35°C
Operating Relative Humidity	0% - 95% non-condensing
Storage Temperature	5°F to 113°F / -15°C to 45°C
Maximum Operating Elevation	10,000 ft / 3,000 m
Maximum Storage Elevation	50,000 ft / 15,000 m
CERTIFICATIONS	
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	1 Year Limited